



## 760144527 | HD SHLF 250LB

**Heavy Duty Tool-less Shelf 250 lb Capacity**

### Dimensions

Depth	696.0 mm   27.4 in
Height	413.4 mm   16.3 in
Width	45.0 mm   1.8 in
Mounting Rail Depth, maximum	742.0 mm   29.2 in
Mounting Rail Depth, minimum	742.0 mm   29.2 in

### General Specifications

Ordering Note	Available in Mexico, Central America, and South America   Available in the United States and Canada	
Cabinet Type	Network cabinet	Server cabinet
Product Type	Shelf	
Rack Units	2	
Color	Black	
Finish	Powder-coated, smooth	
Package, quantity	1	

### Mechanical Specifications

Material Type	Steel
Static Load Rating	113.4 kg   250.0 lb

### Packed Dimensions

Shipping Weight	4.50 kg   9.92 lb
-----------------	-------------------

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

