



760139709 | RK4P58-36A

Rack, 4-Post, (58U), 36 in (914 mm) D x 9 ft (2743 mm) H x 19 in (482.6 mm) W, alum, 12-24 tapped rails, black

Dimensions

Channel Width	3.0 in
Depth	1219.2 mm 48.0 in
Dimensional Standards	EIA-310-D
Height	2743.2 mm 108.0 in
Width	515.6 mm 20.3 in

General Specifications

Product Type	4 post rack
Rack Units	58
Color	Black
Finish	Powder-coated, textured
Includes	Base pan Forty #12 -24 x 1/2 in mounting screws Four vertical rack rails Instruction sheet Twelve 3/8 in split lock washers Twelve 3/8 -16 hex nuts Twelve 3/8 -16 UNC x 1 in hex head bolts Two extruded base angles Two extruded top angles Upper plate support
Package, quantity	1
Packaging Type	Flat packed
Rack Type	EIA 19 in

Mechanical Specifications

Rail Mounting Hole	#12-24
Material Type	Aluminum
Static Load Rating	907.2 kg 2000.0 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

