



103801247 | 110C-4
110 Connecting Block, 4 pair count, 10 per package

Dimensions

Depth	23.62 mm 0.93 in
Height	6.35 mm 0.25 in
Width	30.48 mm 1.20 in

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL

General Specifications

Product Type	Block
Color	White
Lug Attachment	Field attached
Package, quantity	10
Pairs, quantity	4

Mechanical Specifications

Conductor Gauge, stranded	22 AWG 23 AWG 24 AWG 26 AWG
Material Type	Copper alloy
Outlet/Module Contact Plating	Nickel
Plug Insertion Life, minimum	200 times

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

