



106669278 | M40R-J2-246

Insert Panel for M40 Surface Mount Box, holds three RJ45 jacks

Dimensions

Depth	2.03 mm 0.08 in
Height	37.34 mm 1.47 in
Weight	0.01 kg 0.03 lb
Width	66.80 mm 2.63 in

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Mount Type	Surface
Product Type	Surface mount box
Application	Support a copper/fiber intergrated environment
Color	White
Package, quantity	1

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system