



107213605 | 384A  
**Broadband Video Adapter**

## Dimensions

Cable Length	12.00 ft
Housing Length	2.30 in

## Electrical Specifications

Bandwidth	55–550 MHz
Common Mode Rejection, minimum	40 dB
Input Impedance, source	75 ohm, unbalanced
Output Impedance, twisted pair	100 ohm, balanced
Signal to Noise Ratio, minimum	60 dB

## Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	5%–95%, non-condensing
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Product Type	Video adapter
Mount Type	Plug-in
Package, quantity	1

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

