



108009432 | M81C-COUPLER

M81C Coaxial Coupler

- Comes with 4 mounting collars - white, gray, black & ivory

Dimensions

Depth	12.70 mm		0.50 in
Height	17.53 mm		0.69 in
Width	18.54 mm		0.73 in

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	5%–95%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Product Type	Multimedia coupler
Application	Module designed for video applications
Mount Type	Snap-in
Package, quantity	1

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

