



108065814 | M61A-317
M61 Information Outlet Icon Insert for MGS Information Outlet, red

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Color	Red
Product Type	Icon
Package, quantity	25

Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic
---------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

