



108236167 | 2512CAT5PS2-48

PowerSUM 2512 Category 5 U/UTP Patch Panel, 48 port 100BASE-TX, 100BASE-T

Dimensions

Depth	40.64 mm 1.60 in
Height	88.90 mm 3.50 in
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	5
-------------------	---

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	PowerSUM SYSTIMAX®
Cable Type	U/UTP (unshielded)
Product Type	Panel
Total Ports, quantity	48
Color	Black
Package, quantity	1
Rack Type	EIA 19 in
Rack Units	2

Mechanical Specifications

Panel Style	Straight
Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

