



700206725 | MGS400-262

GigaSPEED® XL MGS400 Series Category 6 U/UTP Information Outlet, white

Dimensions

Depth	30.48 mm 1.20 in
Height	20.32 mm 0.80 in
Width	20.32 mm 0.80 in

Electrical Specifications

ANSI/TIA Category	6
Contact Resistance Variation, maximum	20 mOhm
Contact Resistance, maximum	100 mOhm
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	GigaSPEED® XL SYSTIMAX®
Cable Type	U/UTP (unshielded)
Color	White
Product Type	Outlet
Package, quantity	1

Mechanical Specifications

Conductor Gauge, solid	22 AWG 24 AWG 26 AWG
Conductor Gauge, stranded	22 AWG 24 AWG
Conductor Type	Solid Stranded (7 strands)
Material Type	Copper alloy High -impact, flame retardant, thermoplastic
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug

700206725 | MGS400-262

Plug Retention Force, minimum	30 lbf 133 N
Rear Termination Contact Plating	Precious metals
Rear Termination Type	IDC
Wiring	T568A T568B

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2008

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system

