

999903004

**Outdoor Multi-Pair Data Cable, 25 pair**

## Electrical Specifications

---

ANSI/TIA Category	3
Characteristic Impedance	100 ohm
Characteristic Impedance Tolerance	±15 ohm
dc Resistance Unbalance, maximum	3 %
Dielectric Strength, minimum	700 Vac   1000 Vdc

## Environmental Specifications

---

Installation Temperature	-10 °C to +50 °C (+14 °F to +122 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)

## General Specifications

---

Ordering Note	Available in Europe, Middle East, and Africa
---------------	--

## Regulatory Compliance/Certifications

---

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

