



760047662 | VP1PRFTRM VisiPatch® 1-pair Field Termination Cord Plug Kit

This product will be discontinued on: December 31, 2012

Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Product Type	Tool
Color	Dark gray
Package, quantity	100
Pairs, quantity	1

Mechanical Specifications

Conductor Gauge, stranded	24 AWG
Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	18 N 4 lbf
Wiring	VisiPatch®

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

848202800 | 1074C DG 1/24 RVAR (Product Component—not orderable) — GigaSPEED® XL 1074C Category 5e U/UTP Cable, non-plenum, dark gray jacket, 1 pair count, variable length, reel

CC4651643/BU | 5EJ1 GRAY BULK REEL (Product Component—not orderable) — DataPipe® 5EJ1 Category 5e U/UTP Cable, non-plenum, gray jacket, 1 pair count, bulk length, reel