



760038513 | iP-PTF-12-SC-LS

iPatch® LazrSPEED® Pre-Terminated Intelligent Fiber Shelf, SC 12 port duplex

Dimensions

Depth	323.85 mm 12.75 in
Height	44.45 mm 1.75 in
Weight	3.18 kg 7.00 lb
Width	482.60 mm 19.00 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX®
Product Type	Intelligent fiber shelf, preterminated
Color	Black
Includes	Four #12-24 mounting screws Instruction sheet Shelf
Interface	SC
Package, quantity	1
Shelf Movement	Sliding
Total Ports, quantity	12

Mechanical Specifications

Fiber Type	LazrSPEED® 150, 50 µm multimode fiber LazrSPEED® 300, 50 µm multimode fiber LazrSPEED® 550, 50 µm multimode fiber
Material Type	ABS Polycarbonate

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

