



## 760038521 | iP-PTF-12-SC-TS

**iPatch® TeraSPEED® Pre-Terminated Intelligent Fiber Shelf, SC 12 port duplex**

### Dimensions

Depth	323.85 mm   12.75 in
Height	44.45 mm   1.75 in
Weight	3.18 kg   7.00 lb
Width	482.60 mm   19.00 in

### Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel   CE   CSA   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

Brand	iPatch®   SYSTIMAX®
Product Type	Intelligent fiber shelf, preterminated
Color	Black
Includes	Four #12-24 mounting screws   Instruction sheet   Shelf
Interface	SC
Package, quantity	1
Shelf Movement	Sliding
Total Ports, quantity	12

### Mechanical Specifications

Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Material Type	ABS   Polycarbonate

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

