



760073866 | iP-M4200i-24

iPatch® M4200i 24 Port UTP Intelligent Universal Modular Panel without Modules

Dimensions

Depth	25.40 mm 1.00 in
Height	44.45 mm 1.75 in
Weight	0.68 kg 1.50 lb
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	6 6A
-------------------	--------

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE cUL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX®
Product Type	Intelligent copper panel, modular
Color	Black
Includes	Cable management bar Four #12 -24 dog point mounting screws Information outlet removal tool Instruction sheet Panel Two #12 washers Two #12 -24 screws
Package, quantity	1
Total Ports, quantity	24

Mechanical Specifications

Panel Style	Straight
Material Type	ABS Polycarbonate

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

