



760080887 | iP-600A-12-CSC-SMF

iPatch® 600A Fixed SC Single-mode Intelligent Fiber Shelf, 12 port duplex ceramic

Dimensions

Depth	223.52 mm 8.80 in
Height	44.45 mm 1.75 in
Weight	1.81 kg 4.00 lb
Width	482.60 mm 19.00 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX®
Product Type	Intelligent fiber shelf
Color	Black
Includes	Cover Four #12-24 mounting screws Instruction sheet One piece double sided tape One set splice tray holders Shelf Two cable ties Two wire retainers
Interface	SC
Package, quantity	1
Shelf Movement	Fixed
Total Ports, quantity	12

Mechanical Specifications

Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Material Type	ABS Polycarbonate

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

