



760093344 | 360-iP-HD-MOD-LC-LS

SYSTIMAX 360™ iPatch® G2 LazrSPEED® High Density Module

Dimensions

Depth	215.90 mm 8.50 in
Height	82.55 mm 3.25 in
Weight	1.13 kg 2.50 lb
Width	152.40 mm 6.00 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX 360™ SYSTIMAX®
Product Type	Intelligent fiber shelf
Adapters, quantity, rear	4
Color	Black
Color, front	Aqua
Color, rear	Black
Interface Feature, front	Standard
Interface Feature, rear	Reduced footprint
Interface, front	LC
Interface, rear	MPO
Package, quantity	1
Package, quantity	1
Total Ports, quantity, front	48

Mechanical Specifications

Fiber Type	LazrSPEED® 550, 50 µm multimode fiber
Material Type	ABS Polycarbonate

Optical Performance

Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB
Insertion Loss, maximum	0.50 dB

760093344 | 360-iP-HD-MOD-IC-LS

Return Loss, minimum 20.0 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from 0 °C to +60 °C (+32 °F to +140 °F)