



760095562 | 360-iP-PANEL-MGR
SYSTIMAX 360™ iPatch® Panel Manager

Dimensions

Depth	114.30 mm 4.50 in
Height	44.45 mm 1.75 in
Weight	1.02 kg 2.25 lb
Width	457.20 mm 18.00 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 75%, non-condensing
Safety Standard	Austel CE cUL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX 360™ SYSTIMAX®
Product Type	Infrastructure control system
Color	Black Cool gray
Includes	16 in panel bus jumper 7 ft patch cord Forty -four position bus panel Power supply, 1.25A @ 12 Vdc output, 100-240 Vac 50-60 Hz input
Package, quantity	1

Mechanical Specifications

Material Type	ABS Polycarbonate Steel
---------------	-----------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

