



## 760111013 | 3603M-48LC-LS

**InstaPATCH® 360 Ultra High Density Module 48 fiber, LC, LazrSPEED**

### Construction Materials

Fiber Type	LazrSPEED® 550, 50 µm multimode fiber
Total Fibers, quantity	48

### Dimensions

Depth	127.0 mm   5.0 in
Height	12.70 mm   0.50 in
Width	381.0 mm   15.0 in

### Environmental Specifications

Safety Standard	UL
-----------------	----

### General Specifications

Interface, front	LC
Total Ports, quantity, front	24
Color, front	Aqua
Adapters, quantity, front	24
Brand	InstaPATCH® 360   SYSTIMAX 360™   SYSTIMAX®
Interface, rear	MPO
Adapters, quantity, rear	4
Interface Feature, rear	Standard
Color, rear	Gray
Package, quantity	1

### Optical Performance

Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB
Insertion Loss, maximum	0.50 dB
Return Loss, minimum	20.0 dB

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



### \* Footnotes

760111013 | 3603M-48LC-LS

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from 0 °C to +60 °C (+32 °F to +140 °F)