



760111039 | 3603M-48LC-SM

InstaPATCH® 360 Ultra High Density Module 48 fiber, LC, TeraSPEED

Construction Materials

Fiber Type	TeraSPEED®, zero water peak singlemode fiber
Total Fibers, quantity	48

Dimensions

Depth	127.0 mm 5.0 in
Height	12.70 mm 0.50 in
Width	381.0 mm 15.0 in

Environmental Specifications

Safety Standard	UL
-----------------	----

General Specifications

Interface, front	LC
Total Ports, quantity, front	24
Color, front	Blue
Adapters, quantity, front	24
Brand	InstaPATCH® 360 SYSTIMAX 360™ SYSTIMAX®
Interface, rear	MPO
Adapters, quantity, rear	4
Interface Feature, rear	Standard
Color, rear	Gray
Package, quantity	1

Optical Performance

Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB
Insertion Loss, maximum	1.30 dB
Return Loss, minimum	55.0 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



* Footnotes

760111039 | 3603M-48LC-SM

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from 0 °C to +60 °C (+32 °F to +140 °F)