



## 760117408 | 360-PM-KIT-2U-48

**SYSTIMAX 360™ PATCHMAX® Panel Kit, 2U, 48 port**

### Dimensions

Depth, with cable management	10.50 in
Height	88.90 mm   3.50 in
Width	482.60 mm   19.00 in

### Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

Brand	GigaSPEED® X10D   GigaSPEED® XL   PATCHMAX®   SYSTIMAX 360™   SYSTIMAX®
Cable Type	U/UTP (unshielded)
Product Type	Panel
Color	Cool gray   Satin chrome
Package, quantity	1
Rack Type	EIA 19 in
Rack Units	2

### Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic   Powder-coated steel
---------------	---

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

