

760154096 | H61A-226-GREEN

High Density Icon Strip, green, bulk pack

Dimensions

Depth	2.79 mm 0.11 in
Height	13.97 mm 0.55 in
Width	23.62 mm 0.93 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	SYSTIMAX®
Color	Green
Product Type	Icon
Ordering Note	Minimum order quantity, 20 packs
Package, quantity	25

Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic
---------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

