



760158428 | PS42U600W1200D L6-A3333333

InstaPATCH® ZERO Pre-terminated Cabinet, six cord cassettes, left mount A, B, C, D, E and F positions, Category 6A U/UTP patch cords, dark gray jacket, OM4 fiber ruggedized fanouts

Configuration Specifications

ANSI/TIA Category	6A
Cable Types	Mixed media
Fiber Type	LazrSPEED® 550, 50 µm multimode fiber
Jacket Color, copper	Dark gray
Jacket Color, fiber	Aqua
Cassette Location	Left mount, position A Left mount, position B Left mount, position C Left mount, position D Left mount, position E Left mount, position F
Cassette, quantity	6
Port Quantity, copper	72
Port Quantity, fiber	72

Dimensions

Depth	1200.0 mm 47.2 in
Dimensional Standards	EIA-310-E
Height	2000.0 mm 78.7 in
Weight	178.00 kg 392.42 lb
Width	600.0 mm 23.6 in

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

General Specifications

Brand	InstaPATCH® ZERO SYSTIMAX®
Color	Black
Finish	Powder-coated, textured
Includes	Brush baffle Cord bundle mounting bracket Cover plate Fifty M6 clip nuts Four M12 leveling feet One hundred M6 screws
Ordering Note	Available in Mexico, Central America, and South America Available in the United States and Canada
Package, quantity	1
Packaging Type	Assembled
Rack Units	42

Mechanical Specifications

Cable Entry, top	Two front openings 3.4 in X 13.5 in (86 mm x 343 mm) Two rear 4 in (100 mm) openings with protective covers
Casters	Included

760158428 | PS42U600W1200D L6-A333333

Door Material, front	Steel
Door Material, rear	Steel
Door Type, front	Single
Door Type, rear	Double
Door Vent, front	Vented/Fully perforated
Door Vent, rear	Vented/Split perforated
Frame Type	Welded
Lock Type, front	2-Point
Lock Type, rear	1-Point
Material Type	Steel
Side Panels	Not included
Static Load Rating	1451.5 kg 3200.0 lb
Top Panel	Included

Packed Dimensions

Depth	1320.0 mm 52.0 in
Height	2337.0 mm 92.0 in
Shipping Weight	200.00 kg 440.92 lb
Width	1220.0 mm 48.0 in

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

ZC12A3B24LP-F010 — InstaPATCH® ZERO Cord Cassette with twelve Category 6A U/UTP patch cords, dark gray jacket, tail length 10 feet, 24 OM4 Fiber Ruggedized Fanout

- 860474246 | 1095B DG 4/24 RVAR (Product Component—not orderable) — GigaSPEED® X10D 1095B Category 6A U/UTP Cable, non-plenum, dark gray jacket, 4 pair count, variable length, reel
- FLXMXLCAF — LazrSPEED® 550 MPO (male) to LC, InstaPATCH® 360 Ruggedized Fanout Cable, 24-Fiber, Plenum

ZC12A3B24LP-F008 — InstaPATCH® ZERO Cord Cassette with twelve Category 6A U/UTP patch cords, dark gray jacket, tail length 8 feet, 24 OM4 Fiber Ruggedized Fanout

- 860474246 | 1095B DG 4/24 RVAR (Product Component—not orderable) — GigaSPEED® X10D 1095B Category 6A U/UTP Cable, non-plenum, dark gray jacket, 4 pair count, variable length, reel
- FLXMXLCAF — LazrSPEED® 550 MPO (male) to LC, InstaPATCH® 360 Ruggedized Fanout Cable, 24-Fiber, Plenum

ZC12A3B24LP-F006 — InstaPATCH® ZERO Cord Cassette with twelve Category 6A U/UTP patch cords, dark gray jacket, tail length 6 feet, 24 OM4 Fiber Ruggedized Fanout

- 860474246 | 1095B DG 4/24 RVAR (Product Component—not orderable) — GigaSPEED® X10D 1095B Category 6A U/UTP Cable, non-plenum, dark gray jacket, 4 pair count, variable length, reel

760158428 | PS42U600W1200D L6-A3333333

- FLXMXLCAF — LazrSPEED® 550 MPO (male) to LC, InstaPATCH® 360 Ruggedized Fanout Cable, 24-Fiber, Plenum

* Footnotes

Cassette Location	Left mount: Cassette located on left side of cabinet when viewed from front; Right mount: Cassette located on right side of cabinet when viewed from front
-------------------	---