Product Specifications

COMMSCOPE®

760158048 | PS42U600W1200D R2-B3001100

InstaPATCH® ZERO Pre-terminated Cabinet, two cord cassettes, right mount C and D positions, Category 6 U/UTP patch cords, dark gray jacket

Configuration Specifications

ANSI/TIA Category	6
Cable Types	U/UTP (unshielded)
Jacket Color, copper	Dark gray
Cassette Location	Right mount, position C | Right mount, position D
Cassette, quantity	2
Port Quantity, copper	24

Dimensions

Depth	1200.0 mm | 47.2 in
Dimensional Standards	EIA-310-E
Height	2000.0 mm | 78.7 in
Weight	146.00 kg | 321.87 lb
Width	600.0 mm | 23.6 in

Environmental Specifications

Safety Standard	cUL | UL

General Specifications

Brand	InstaPATCH® ZERO | SYSTIMAX®
Color	Black
Finish	Powder-coated, textured
Includes	Brush baffle | Cord bundle mounting bracket | Cover plate | Fifty M6 clip nuts | Four M12 leveling feet | One hundred M6 screws
Ordering Note	Available in Mexico, Central America, and South America | Available in the United States and Canada
Package, quantity	1
Packaging Type	Assembled
Rack Units	42

Mechanical Specifications

Cable Entry, top	Two front openings 3.4 in X 13.5 in (86 mm x 343 mm) | Two rear 4 in (100 mm) openings with protective covers
Casters	Included
Door Material, front	Steel
Door Material, rear	Steel
Door Type, front	Single
Door Type, rear	Double
Door Vent, front	Vented/Fully perforated

©2012 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 19, 2012

Product Specifications

760158048 | PS42U600W1200D R2-B3001100

Door Vent, rear	Vented/Split perforated
Frame Type	Welded
Lock Type, front	2-Point
Lock Type, rear	1-Point
Material Type	Steel
Side Panels	Not included
Static Load Rating	1451.5 kg | 3200.0 lb
Top Panel	Included

Packed Dimensions

Depth	1320.0 mm | 52.0 in
Height	2337.0 mm | 92.0 in
Shipping Weight	168.00 kg | 370.38 lb
Width	1220.0 mm | 48.0 in

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

ZC12A2B0000-F008 — InstaPATCH® ZERO Cord Cassette with twelve Category 6A U/UTP patch cords, light blue jacket, tail length 8 feet

- 860474253 | 1095B LB 4/24 RVAR (Product Component—not orderable) — GigaSPEED® X10D 1095B Category 6A U/UTP Cable, non-plenum, light blue jacket, 4 pair count, variable length, reel

* Footnotes

Cassette Location	Left mount: Cassette located on left side of cabinet when viewed from front; Right mount: Cassette located on right side of cabinet when viewed from front

©2012 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 19, 2012