



## 760163824 | 360-iP-MFTPA-E-1U-BLANK SYSTIMAX 360™ iPatch® FTP Angled Evolve Panel, 24 port without modules

### Dimensions

Depth	266.70 mm   10.50 in
Diameter Over Dielectric, maximum	1.168 mm   0.046 in
Diameter Over Dielectric, minimum	0.762 mm   0.030 in
Height	44.45 mm   1.75 in
Weight	0.73 kg   1.60 lb
Width	482.60 mm   19.00 in

### Electrical Specifications

ANSI/TIA Category	6   6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

### Environmental Specifications

Flammability Rating	UL 94 V-7
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA   CE   cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

Brand	iPatch®   SYSTIMAX 360™   SYSTIMAX®
Product Type	Intelligent copper panel
Color	Cool gray
Includes	Cable management bar   Four "A" labels   Four #12 -24 mounting screws   Instruction sheet   Panel   Twenty -four cable ties
Intelligence Type	iPatch® enabled
Package, quantity	1
Total Ports, quantity	24

### Mechanical Specifications

Panel Style	Angled
Material Type	ABS   Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	133 N   30 lbf

760163824 | 360-iP-MFTPA-E-1U-BLANK

Wiring

T568A | T568B

## Regulatory Compliance/Certifications

---

**Agency**

RoHS 2002/95/EC  
ISO 9001:2008

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system

