



108065673 | M61A-112

**M61 Information Outlet Icon Insert for MGS Information Outlet, orange**

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Color	Orange
Product Type	Icon
Package, quantity	25

## Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic
---------------	---

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

