

LCD-501



LCD-501X3



#### MODEL NUMBERS

LCD-501

LCD-501X3 Three Monitors in Rack Mount

#### DESCRIPTION

Wide operating power range (10 ~ 30VDC)

Picture on demand/power saving feature

Front mounted stereo headphone jack for private listening (no built-in speakers)

Slim space saving design

Compact and light weight for easy installation or mobile use

Low power consumption

Case made of durable ABS plastic

Active matrix technology allows wide viewing angle

Front controls for color, brightness and audio volume

A/C adaptor, Part No. AC-2000, included

#### OPTIONAL ACCESSORIES

BP-563 Rechargeable 2200mAH battery pack provides approximately 5 hrs. of operation

DC-12 Car Cord

DC-12D Dual car cord

HS-1 Hot Shoe mount

LM-BR-501 Brass Flush Mount Kit  
Requires rear access to install  
Dimensions (WH): 5.82" x 5.43"  
Installer's cut-out: 5.15"(W) x 4.44"(H)

MB-72M Metal Mounting Bracket

MB-1 Desk Stand

WM-1 Wall mount bracket

#### SPECIFICATIONS (LCD-501)

Resolution 600(H) x 234(V) dots

Brightness Rating 240 cd/m<sup>2</sup> (Nit)

Dot Pitch 0.171(H) x 0.316(V)

Contrast Ratio 120:1

Display 5" TFT LCD active matrix

Active Area 102.6(H) x 73.9(V)

Back Light CCFT

Input Signal NTSC/PAL (auto switching)

Number of Pixels 140,400

Pixel Configuration Stripe

Operating Power Range 10 ~ 30 VDC

Input Signal Level 1.0V P-P (positive) 75 Ohm

Audio Input Level 1.0V P-P

Audio output 0.3 W

Audio Input Impedance 10K ohm

Audio Band Width 15 KHz

Viewing angle (L/R/T/B) 55°/55°/15°/35°

Dimensions (WHD) 146 x 105 x 30.5mm/5.7" x 4.1" x 1.2"

Monitor Mounting Mounting pad with ¼ - 20 threaded socket

Actual Visible screen size (WH) 102 x 74mm / 4" x 2.9"

Operating temperature 50 ~ 104°F or 10 ~ 40°C, 85% RH max.

Storage temperature -4 ~ 140°F or -20 ~ 60°C, 85% RH max.

Power Requirement / Consumption 12VDC (1A, + pin) / 7 W (max.)

DIN Cable Connections  
RCA video IN  
RCA right audio IN  
RCA left audio IN  
2.1 DC IN jack

LCD-501 Weight **Net** 363g / 12.8oz **Gross** 1.2 kg / 2.7 lbs  
LCD-501X3 Weight **Net** 2.4kg / 5.3lbs **Gross** 5.3kg / 11.8 lbs