



Designed to Flush Mount with Box Eliminator.

Durable Construction.

Complemented by a Broad Range of Voice/Data/Video Modules.

#### FEATURES

- Provides a rear loading, snap in, flush mounting of Hubbell **XCELERATOR™** Jacks and Audio/Video keystone connectors.
- Available in single and double-gang.
- All IFP plates are supplied with paper labels, clear screw covers, and color-matched screw covers.
- Individual-port configurations allow specification flexibility.

#### SPECIFICATIONS

- ◆ UL listed and cUL certified.
- ◆ ANSI/TIA/EIA-606-A station labeling capability.
- ◆ UL 94V-0 rated flame-retardant material.
- ◆ Mounts to standard NEMA openings and boxes.

## Plates, Rear-Loading



Hubbell's IFP Rear-Loading plates provide an attractive, sleek new style to the workstation. The IFP plates add security at the workstation through rear loading. TIA/EIA-606 station labeling capability is provided through two labeling options: paper labels with clear covers, or color-matched covers for use with adhesive labels.

These plate features include vertical orientation of all port openings and flush mounting with box eliminators. Available in 6 colors including black which is ideal for use with office furniture systems.

**ORDERING INFORMATION**

**IFP Face Plates, Rear-Loading**

**Order Information**

Delivery Single-Gang: 1 per bag/Carton of 25. Delivery Double-Gang 1 per bag/Carton of 10.





Size	1-port	2-port	3-port	4-port	6-port	6-port	9-port	12-port
Catalog No.	<b>IFP11XX</b>	<b>IFP12XX</b>	<b>IFP13XX</b>	<b>IFP14XX</b>	<b>IFP16XX</b>	<b>IFP26XX</b>	<b>IFP29XX</b>	<b>IFP212XX</b>


XX = Color: 'BK' = Black; 'EI' = Electric Ivory; 'GY' = Gray; 'OW' = Office White; 'TI' = Telco Ivory; 'W' = White.

**ACCESSORIES**


**Box Eliminators**

Description	Catalog No.	
Single-gang used in place of an electrical box, inserts into, and secures to a drywall opening providing a means to mount a 1-gang plate.	<b>BRBE1</b>	
Double-gang used in place of an electrical box, inserts into, and secures to a drywall opening providing a means to mount a 2-gang plate.	<b>BRBE2</b>	

**Patch Cords, Category 6 and 5e**

	Catalog No.	
Category 5e	<b>PCX5EXX*</b>	
Category 6	<b>PCX6XX**</b>	
<b>XX</b> = Standard Color:		
'B' = Blue; 'BK' = Black;		
'GY' = Gray; 'Y' = Yellow		
For other colors replace color designation with one of the following:		
OR = Orange, R = Red, GN = Green, P = Purple, W = White		
* = Standard Length: '01'=1'; '03'=3'; '05'=5'; '07'=7'; '10'=10'; '15'=15'; '20'=20'; '25'=25'; '30'=30'; '35'=35'; '40'=40'; '45'=45'; '50'=50'; '55'=55'; '60'=60'; '75'=75'; '100'=100'		
** = Standard Length: '03' = 3; '06' = 6; '08' = 8; '10' = 10; '12' = 12; '16' = 16; '20' = 20'		

**XCELERATOR™ Jacks, Category 6 and 5e**

	Catalog No.	
Category 5e	<b>HXJ5EXX</b>	
Category 6	<b>HXJ6XX</b>	
XX = Color:		
'AL' = Almond	'OW' = Office White	
'B' = Blue	'OR' = Orange	
'BK' = Black	'P25' = Purple*	
'EI' = Electric Ivory	'R' = Red	
'GL25' = Gold*	'TI' = Telco Ivory	
'GY' = Gray	'W' = White	
'GN' = Green	'Y' = Yellow	
* 25-packs only.		

**UTP Cable, SPEEDGAIN® Category 5E, 4-Pair**

Color	Catalog No. Riser		Catalog No. Plenum	
	Spool	REELEX*	Spool	REELEX*
Blue	<b>C5EPSRB</b>	<b>C5EPRRB</b>	<b>C5EPSPB</b>	<b>C5EPRPB</b>
Gray	<b>C5EPSRGY</b>	<b>C5EPRRGY</b>	<b>C5EPSPGY</b>	<b>C5EPRPGY</b>
White	<b>C5EPSRW</b>	<b>C5EPRRW</b>	<b>C5EPSPW</b>	<b>C5EPRPW</b>
Yellow	<b>C5EPSRY</b>	<b>C5EPRRY</b>	<b>C5EPSPY</b>	<b>C5EPRPY</b>
* REELEX is licensed and patented by Windings Inc.				

**UTP Cable, NEXTSPEED® Category 6, 4-Pair**

Color	Catalog No. Riser		Catalog No. Plenum	
	Spool	REELEX*	Spool	REELEX*
Blue	<b>C6SRB</b>	<b>C6RRB</b>	<b>C6SPB</b>	<b>C6RPB</b>
Gray	<b>C6SRGY</b>	<b>C6RRGY</b>	<b>C6SPGY</b>	<b>C6RPGY</b>
White	<b>C6SRW</b>	<b>C6RRW</b>	<b>C6SPW</b>	<b>C6RPW</b>
Yellow	<b>C6SRY</b>	<b>C6RRY</b>	<b>C6SPY</b>	<b>C6RPY</b>
* REELEX is licensed and patented by Windings Inc.				

**Labeling**

Hubbell Labeling Solutions*	Catalog No.
Face Plate Labels, white adhesive	<b>XPLFPA10W</b>
Face Plate Labels, white paper	<b>XPLFP10W</b>
Face Plate Labels, clear adhesive	<b>XPLFPA10C</b>
Port Icon Labels, white adhesive	<b>XPLIPA10W</b>
Port Icon Labels, clear adhesive	<b>XPLIPA10C</b>

**Pre-Printed Icon Label Booklets (5-packs)**

Icon Labels, clear adhesive with black text	<b>XPICONS</b>
Icon Labels, clear adhesive with white text	<b>XPICONSW</b>

\* Contact our website at [www.hubbell-premise.com](http://www.hubbell-premise.com) for our unique Labeling Software.



**Hubbell Premise Wiring**

HUBBELL INCORPORATED (Delaware)  
 14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005  
 Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

**Worldwide Locations**

Hubbell Premise Wiring, Asia Pacific	852-2836-7131	Fax: 852-2836-7132	Hubbell Premise Wiring, Latin America	305-408-4501	Fax: 305-408-8201
Hubbell Canada Inc.	905-839-1138	Fax: 905-839-9108	Hubbell de Mexico, S.A. de C.V.	(5255) 9151-9999	Fax: (5255) 9151-9989
Hubbell Premise Wiring, Central America	506-309-4158	Fax: 506-260-1616	Hubbell Premise Wiring, Middle East	971-4-393-4192	Fax: 971-4-393-4194
Hubbell Premise Wiring, China	8621-6309-0119	Fax: 8621-6309-0122	Hubbell-Taian Co., Ltd., Taiwan	886-2-2522-1862	Fax: 886-2-2522-1872
Hubbell Premise Wiring, Colombia	571-245-8940	Fax: 571-340-0925	Hubbell Premise Wiring, Turkey	90-216-313-5016	Fax: 90-216-414-8148
Hubbell Premise Wiring, Europe	44-01283 500500	Fax: 44-01283 500400	Hubbell Premise Wiring, Venezuela	58-416-680-7453	Fax: 58-281-274-7900
Hubbell Int'l. Inc., Korea Branch	82-2-(0)2607-1363	Fax: 82-2-(0)2603-7386			