


880 Series[™] Floor Boxes

Single-Service Round Floor Boxes

Wiremold® 880 Series Floor Box provides an excellent solution for the low density power or communication requirements in open space areas. The 880 Series brings the power or communication service directly to the workstation. The 880 Series comes in a cast iron version for on grade applications and an economical stamped steel version for above grade applications. The 880 Series is supported by one of the most complete lines of brass, brushed aluminum, and nonmetallic activations in the industry. Some applications for the 880 Series Floor Box are retail facilities, commercial offices, hotels, and financial institutions.





Protection from water, dirt, and debris.

880 Series Steel Floor Box.

FEATURES & BENEFITS

- Snap down ring assembly for steel floor boxes. Labor saver.
- **Fully adjustable box.** Can adjust before and after concrete pour. Lower installed cost.
- Handles single and duplex devices. Economical solution for low density power requirements.
- All 895 and 896 Cover Plates fit 885B, 886B, 887B. and 889B Floor Boxes. More activation options to meet any decor.
- **Two different depths.** Accommodates various pour depths and wiring capacity requirements.
- TopGuard protection. An integral design which keeps out water, dirt, and debris from the power and communication compartments. Whenever you see the TopGuard protection icon applied to any Wiremold product, you will know that the product meets and exceeds the new UL scrub water exclusion requirement.
- UL Listed to U.S. and Canadian safety standards for tile, terrazzo, and the UL requirements under UL514A and UL514C for the scrub water exclusion test for carpet and wood floors.




880 Series Cast Iron Floor Box with 896TCK Brass Communications or Power Cover.



The 880 Series family of steel and cast-iron Floor Boxes.

880 Series Steel Floor Box Ordering Information


Catalog No./Item



Description/Specifications

Floor Box - Stamped steel, shallow single-service.

TECHNICAL SPECIFICATIONS							
		Adjus	tment				
Class	Catalog No.	Before the Pour	After the Pour	Capacity Cu In	Knockouts or Conduit Openings		
Concrete- Tight (Steel)	885B	1 3/4" [44mm]	1/2" [12.7mm]	29.5 [484ml]	Four Sides - (1) 1/2" [12.7mm] (1) 3/4" [19.1mm] Bottom - (2) 1/2" [12.7mm] (2) 3/4" [19.1mm]		




Floor Box – Stamped steel, deep single-service.

TECHNICAL SPECIFICATIONS							
Class	Catalog No.	Adjus Before the Pour	tment After the Pour	Capacity Cu In	Knockouts or Conduit Openings		
Concrete- Tight (Steel)	886B	1 3/4" [44mm]	1/2" [12.7mm]	39 [639ml]	Two Sides - (1) 1/2" [12.7n (1) 3/4" [19.1n (1) 3/4" [19.1n (1) 1" [25mn (1) 1" [25mn (2) 1/2" [12.7n (2) 3/4" [19.1n	າm] າm] າ] າm]	

880 Series Cast-Iron Floor Box Ordering Information


Catalog No./Item



Description/Specifications

Floor Box - Cast-iron, shallow single-service.

Technical Specifications						
Adjustment		tment				
Class	Catalog	Before	After	Capacity	Knockouts or	
	No.	the Pour	the Pour	Cu In	Conduit Openings	
Watertight	887B	2"	1/2"	24.7	Two Sides – (1) 1/2" [12.7mm]	
(Cast-Iron)		[51mm]	[12.7mm]	[405ml]	Two Sides – (1) 3/4" [19.1mm]	




Floor Box – Cast-iron, deep single-service.

		Adjustment			
Class	Catalog	Before	After	Capacity	Knockouts or
	No.	the Pour	the Pour	Cu In	Conduit Openings
Watertight	889B	2"	1/2"	40	Two Sides – (1) 1" [25mm]
(Cast-Iron)		[51mm]	[12.7mm]	[665ml]	Two Sides – (1) 1 1/4"[19.1mr

L	over Plates for 880 Series Fl	oor Boxes Ordering I	nformation
Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
895 895TCAL 5 1/2" [140mm]	Duplex Cover Plate with Flip Lid – Brass (895) or brushed aluminum (895TCAL) duplex cover plate with flip lids, 5 1/2" [140mm] for carpet.	895P-AL 5 1/2" [140mm]	Duplex Cover Plate – Aluminum polycarbonate duplex cover plate with flip lids for carpet.
895T 895TAL 4 1/4" [108mm]	Duplex Cover Plate with Flip Lid – Brass (895T) or brushed aluminum (895TAL) duplex cover plate with flip lids, 4 1/4" [108mm] for tile.	896 5 1/2" [140mm]	Communications or Power Cover Plate – Brass communications or power cover plate with 2 5/8" [67mm] threaded opening for carpet. Sold without abandon plug.
895SP 895SPCAL 5 1/2" [140mm]	Cover Plate with Two Screw Plate Openings – Brass (895SP) or brushed aluminum (895SPAL) cover plate with two 1 1/2" [38mm] screw plug openings, 5 1/2" [140mm] for carpet.	896T 4 1/4" [108mm]	Communications or Power Cover Plate – Brass communications or power cover plate with 2 5/8" [67mm] threaded opening for carpet. Sold without abandon plug.
895TSP 4 1/4" [108mm]	Cover Plate with Two Screw Plate Openings – Brass cover plate with two 1 1/2" [38mm] screw plug openings, 4 1/4" [108mm] for tile.	896CK 5 1/2"	Communications or Power Cover Plate – Brass communications or power cover plate with 2 1/4" [57mm] threaded opening for carpet.
895GFI 895GFICAL 5 1/2" [140mm]	GFI Receptacle Cover Plate – Brass (895GFI) or brushed aluminum (895GFICAL) GFI receptacle cover plate, 5 1/2" [140mm] for carpet.	896TCK	Communications or Power Cover Plate – Brass communications or power cover plate with 2 1/4" [57mm] threaded opening for carpet.
895TGFI 895TGFIAL 4 1/4" [108mm]	GFI Receptacle Cover Plate – Brass (895TGFI) or brushed aluminum (895TGFIAL) GFI receptacle cover plate, 4 1/4" [108mm] for tile.	896CK-1/2 896CKAL-1/2 5 1/2" [140mm]	Communications or Power Cover Plate – Brass (896CK-1/2) or brushed aluminum (896CKAL-1/2) cover plate with 1/2" [12.7mm] threaded opening 5 1/2" [140mm] for carpet.
895P-BLK 5 1/2" [140mm]	Duplex Cover Plate – Black polycarbonate duplex cover plate with flip lids for carpet.	896TCK-1/2 896TCKAL-1/2	Communications or Power Cover Plate – Brass (896TCK-1/2) or brushed aluminum (896TCKAL-1/2) cover plate with 1/2" [12.7mm]) threaded opening, 4 1/4" [108mm] for tile.
895P-BRN 5 1/2" [140mm]	Duplex Cover Plate – Brown polycarbonate duplex cover plate with flip lids for carpet.	[108mm] 896CK-3/4 5 1/2" [140mm]	Communications or Power Cover Plate – Brass cover plate with 3/4" [19.1mm] threaded opening for carpet.
895P-BRZ 5 1/2"	Duplex Cover Plate – Bronze polycarbonate duplex cover plate with flip lids for carpet.	896TCK-3/4	Communications or Power Cover Plate – Brass cover plate with 3/4" [19.1mm] threaded opening for tile.

Cover	⁻ Plates for 880 Series Floor	Bo	oxes Ordering Infor	mation (continued)
Catalog No./Item	Description/Specifications		Catalog No./Item	Description/Specifications
896CK-1	Communications or Power Cover Plate – Brass cover plate with 1" [25mm] threaded opening for carpet.		896PCK-BRN	Communications or Power Cover Plate – Brown polycarbonate communications or power cover plate. Includes one plug with 3/4" [19mm] opening, one plug with 1" [25mm] opening, and one plug with 2 5/8" [67mm] opening. For
896TCK-1	Communications or Power Cover Plate – Brass cover plate with			pass-through only.
4 1/4" [108mm] 896PCK-BLK	1" [25mm] threaded opening for tile. Communications or Power Cover Plate – Black polycarbonate communications or power cover plate. Includes one plug with 3/4" [19mm] opening, one plug with 3/4" [25mm] opening, and one plug with 2 5/8" [67mm] opening. For pass-through only.		896PCK-BRZ	Communications or Power Cover Plate – Bronze polycarbonate communications or power cover plate. Includes one plug with 3/4" [19mm] opening, one plug with 1" [25mm] opening, and one plug with 2 5/8" [67mm] opening. For pass-through only.
5 1/2" [140mm]			896PCK-AL	Communications or Power Cover Plate – Aluminum polycarbonate communications or power cover plate. Includes one plug with 3/4" [19mm] opening, one plug with 1" [25mm] opening, and one plug with 2 5/8" [67mm] opening. For pass-through only.





WIREMOLD

U.S. and International: 60 Woodlawn Street • West Hartford, CT 06110 1-800-621-0049 • FAX 860-232-2062 • Outside U.S. 860-233-6251 Canada: 570 Applewood Crescent • Vaughan, Ontario L4K 4B4 1-800-723-5175 • FAX 905-738-9721