

# Keystone Recessed F-conn 75 Ohm White

OR-KSFCNR-88



Ortronics F-connectors are often used with RG-6 and RG-59 75 ohm coaxial cable to connect equipment supporting cable TV(CATV), satellite TV, close circuit TV(CCTV), and security cameras.



## features & benefits

**Recessed design:** Provides a more flush aesthetic look.

**Low profile connector:** Allows furniture to be placed closer to the wall.

**Designed for multiple coax cable styles:** Accepts both push-style and screw-style.

**75 Ohm F-connector:** Ideal for cable/satellite TV, cable modems, and security cameras.

**TechChoice keystone footprint:** Fits in all TechChoice faceplates and housings.

**Rear loading module:** Allows for termination before and during the construction process.

**Integrates with Legrand | Wiremold :** Can be used in raceway, floor boxes, Poke-Thru, and work surface portals.

## specifications

### General Info

Category Performance Application: F-connector

Footprint: Keystone

Number Of Ports: 1-port

Termination: Female to Female Coupler

Typical Applications: Cable TV(CATV), closed circuit TV (CCTV), satellite TV, security cameras, cable modems

### Listing Agencies/Third Party Information

CUL Listing No: E131600

UL Listing No: E131600

## **Construction Information**

Component1: Plastic TechChoice Keystone Housing  
Material1: High Impact Thermoplastic ABS 94V-0

## **Dimensions**

Depth Metric: 22.23  
Depth U S: 0.875

## **Technical Information**

Connection Method: Accepts push-on or screw-on style coax cables  
Ohm Value: 75 Ohm  
Performance Rating: 3GHz