

TracJack Module F Connector F/F, Fog White

OR-63700006



TracJack Module provides a single F-connector coupler F/F with under .2dB of insertion loss at 2GHz (1/3 the loss of standard models). TracJack is a versatile single jack solution in a front-load footprint which allows a choice of up to six jacks/connectors to fit in a single gang plate

features & benefits

- F Connector coupler F/F
- Front removable
- Standard TracJack footprint



specifications

General Info

Category Performance Application: F Conn Coax
Color: Fog White
Footprint: TracJack
Number Of Ports: 2-port

Listing Agencies/Third Party Information

CUL Listing No: E131600
UL Listing No: E131600

Construction Information

Component1: Plastic Series II Housing
Component2: F Connector female/female coupler
Material1: High Impact Thermoplastic ABS 94V-0
Material2: Feed-through, RG6/59 (G-F81TN)

Dimensions

Depth Metric: 14.48 mm
Height Metric: 23.37 mm
Height U S: .92"
Width Metric: 18.54 mm

Buy American Act Compliance

Country of Origin: MALAYSIA
Buy American Act Status: Exception
Notes: Contact Customer Support for Buy American Act options