

25-Pair Voice Grade Cable Assembly, M/M, 25'

OR-804025PP025-1GY



25-Pair Voice Grade Cable Assembly, M/M, 25'

features & benefits



- Factory terminated voice grade cables
- Supported by a family of lengths and terminations
- 24 AWG solid copper construction

specifications

General Info

Cable Type: 25-Pair UTP Non Plenum

Color Cable Jacket: Gray

Termination: 50-Pin (RJ21) M/M

Typical Applications: Voice equipment, connectorized blocks

Listing Agencies/Third Party Information

CSA Listing Info: LR 90894

CUL Listing No: E131601

UL Listing No: E131600

Construction Information

Component1: 25-Pair, 24 AWG, voice grade cable

Component2: 50-Pin male telco connector (RJ21)

Finish Plating2: 30 Micro inches of gold over nickel plating in mating contact area

Material1: 24 AWG, solid copper conductors, PVC insulation, twisted pairs, PVC jacket

Material2: High strength copper alloy contacts| High impact Thermo Plastic housings and covers

Dimensions

Diameter Metric: 8.7 mm

Diameter U S: 0.34"

Length Metric: 7.62 m

Cord Information

Connector Type End One: 50-Pin telco connector - male

Connector Type End Two: 50-Pin telco connector - male

Jacket Color: Gray

Jacket Rating: CMR/PVC

Cord Length U S: 25'

Pinning: Pin 1 to 1 standard 25-pair color code

Technical Information

Category Rating: Category 1

Ohm Value: 100

Performance Rating: Voice

Sort Termination: 8

Wire Gauge: 24 AWG

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant