

Clarity 6 110 Block Kit, with legs, Category 6, 288-pair, 300-pair footprint

OR-110ABC6300



Clarity 6 110 Block Kit, with legs, Category 6, 288-pair, 300-pair footprint

features & benefits



- ETL third party tested and verified Category 6 performance.
- Standard 300-pair 110 footprint
- High density design
- Internal signal feedback technique
- Color-coded C6110C4 connecting blocks
- Provides a termination that is more transparent to the signal
- Backward compatible to Category 3, 5 and 5e
- New and improved labeling system
- Supports consolidation point applications

specifications

General Info

Pair Count: 300

Performance Category: Category 6

Listing Agencies/Third Party Information

CUL Listing No: E131599

UL Listing No: E131599

Construction Information

Component1: 100-pair Block with legs

Component2: C6110C4 Connector Housing

Component3: C110C4 IDC Contact
Component4: Label Holder Side Mount
Component5: Designation Holder/Cover
Material1: Polycarbonate UL94V-0
Material2: Polycarbonate UL94V-0
Material3: Phosphor Bronze 90/10 Tin Lead Plating
Material4: GE Lexan 940
Material5: PVC

Dimensions

Depth Metric: 274 mm
Height Metric: 83 mm
Height U S: 3.25"
Width Metric: 272 mm

Technical Information

Product Fits Into: Backboard, Rack Mount Panel

Buy American Act Compliance

Country of Origin: MALAYSIA
Buy American Act Status: Exception
Notes: Contact Customer Support for Buy American Act options