

## Clarity 5E Modular Patch Cord, 7', orange

OR-MC5E07-03



Clarity 5E Premium Category 5e Modular Patch Cord, orange, 7', Category 5e, four-pair UTP stranded 24 AWG PVC/CM, center tuned with Clarity 5E connecting hardware for optimum Category 5e installed performance using Ortronics Paralign 2 pair-positioning technology



### features & benefits

- **ETL third party tested and verified to TIA/EIA 568B.2 Category 5e component specifications:** Ensures Category 5e component performance.
- **Each cord is factory tested:** Ensures every cord shipped meets Category 6 component specifications.
- **Center tuned technology:** Elevates the performance of Clarity 6 connector union.
- **Paralign 2 pair-positioning technology:** Maintains pair integrity through the plug termination allowing mating hardware to be designed/tuned to these cords.
- **Snagless plug design:** Protects plugs when pulling through pathways or cable managers.
- **Premium conductor cordage:** Reliable performance and durable cord life.
- **Compatible with both T568A and T568B wiring:** Provides universal wiring ability.
- **Improved signal to noise ratio:** More transparent signal path is field measurable in a link or channel.
- **Backwards compatible to Category 3, 5, and 5e:** Supports lower category installations and components.

### specifications

#### General Info

Cable Type: Four-pair stranded UTP non-plenum

Color Cable Jacket: Orange

Termination: 8-Pos Mod

Typical Applications: 10Base-T 100Base-TX 1000Base-T 1000Base-TX 155 Mb/s ATM 1 Gb/s ATM (CB1G)

### **Listing Agencies/Third Party Information**

ETL Listing No: COC 5e PATCH CORD

ETL Standard: Yes

FCC Standard: Yes

### **Construction Information**

Component1: Cable

Component2: Eight-position plug assembly

Component3: Modular plug IDC contacts

Component4: Paralign 2 pair segregation and strain relief

Finish Plating3: 50 Micro inch elective gold plating over nickel

Material1: 24 AWG bare copper stranded conductors, PVC insulation, PVC jacket

Material2: Polycarbonate plug housing and conductor positioning sled

Material3: Phosphor-bronze contacts

Material4: Molded Polypropylene Copolymer

### **Dimensions**

Diameter Metric: 7.1 mm

Diameter U S: 0.28"

Length U S: 7'

Length Metric: 2.14 m

### **Cord Information**

Connector Type End One: Plug, HSG, eight-contact, RJ45, high performance

Connector Type End Two: Plug, HSG, eight-contact, RJ45, high performance

Jacket Color: Orange

Jacket Rating: CM

Cord Length U S: 7'

Min Bend Radius: 1.00"

Pinning: Straight 1-1, 2-2, 3-3, etc.

### **Technical Information**

Category Rating: Category 5e

Ohm Value: 100

Performance Rating: Category 5e

Sort Termination: 3

Wire Gauge: 24 AWG

### **Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant