

# Clarity 6 Modular Patch Cord, 7', black

OR-MC607-00



Clarity 6 Modular Patch Cord, black, 7', Category 6, four-pair UTP stranded 24 AWG PVC/CM, center tuned with Clarity 6 connecting hardware for optimum Category 6 installed performance using Ortronics Paralign 2 pair-positioning technology

## features & benefits

- ETL third party tested and verified to TIA/EIA 568B.2-1 Category 6 component specifications: Ensures Category 6 component performance.
- Each cord is factory tested: Ensures every cord shipped meets Category 6 component specifications.
- Center tuned technology: Elevates the performance of Clarity 6 connector union.
- Paralign 2 pair-positioning technology: Maintains pair integrity through the plug termination allowing mating hardware to be designed/tuned to these cords.
- **Snagless plug design:** Protects plugs when pulling through pathways or cable managers.
- **Premium conductor cordage:** Reliable performance and durable cord life.
- Compatible with both T568A and T568B wiring: Provides universal wiring ability.
- **Improved signal to noise ratio:** More transparent signal path is field measurable in a link or channel.
- Backwards compatible to Category 3, 5, and 5e: Supports lower category installations and components.

# specifications

#### **General Info**

Cable Type: Four-pair stranded UTP non-plenum

Color Cable Jacket: Black Termination: 8-Pos Mod

Typical Applications: IEEE 802.3 1000Base-T (Gigabit Ethernet), TIA/EIA-854 1000Base-TX, ATM CB1G

#### **Listing Agencies/Third Party Information**

ETL Listing No: 3013270-006

ETL Standard: Yes FCC Standard: Yes

#### **Construction Information**

Component1: Cable

Component2: Eight-position plug assembly Component3: Modular plug IDC contacts

Component4: Paralign 2 pair segregation and strain relief Finish Plating3: 50 Micro inch elective gold plating over nickel

Material1: 24 AWG bare copper stranded conductors, PVC insulation, PVC jacket

Material2: Polycarbonate plug housing and conductor positioning sled

Material3: Phosphor-bronze contacts

Material4: Molded Polypropylene Copolymer

#### **Dimensions**

Diameter Metric: 7.5 mm Diameter U S: 0.29" Length Metric: 2.13 m

#### **Cord Information**

Connector Type End One: Plug, HSG, eight-contact, RJ45, high performance Connector Type End Two: Plug, HSG, eight-contact, RJ45, high performance

Jacket Color: Black Jacket Rating: CM Cord Length U S: 7' Min Bend Radius: 1.00"

Pinning: Straight 1-1, 2-2, 3-3, etc.

#### **Technical Information**

Category Rating: Category 6

Ohm Value: 100

Performance Rating: Category 6

Sort Termination: 3 Wire Gauge: 24 AWG

### **Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant