

## Clarity 10G modular patch cord, 15', green

OR-MC61015-05



Clarity 10G modular patch cord, green, 15', 10 Gigabit, four-pair UTP stranded 26 AWG PVC/CM, center tuned with Clarity connecting hardware for optimum installed performance using Ortronics Paralign 2 pair-positioning technology.



### features & benefits

- **ETL third party tested and verified to TIA/EIA 568B.2-10 10G channel specifications:** Ensures Category 6A component performance.
- **Each cord is factory tested:** Ensures every cord shipped meets Category 6 component specifications.
- **Center tuned technology:** Elevates the performance of Clarity 6 connector union.
- **Paralign 2 pair-positioning technology:** Maintains pair integrity through the plug termination allowing mating hardware to be designed/tuned to these cords.
- **Snagless plug design:** Protects plugs when pulling through pathways or cable managers.
- **Premium conductor cordage:** Reliable performance and durable cord life.
- **Compatible with both T568A and T568B wiring:** Provides universal wiring ability.
- **Improved signal to noise ratio:** More transparent signal path is field measurable in a link or channel.
- **Backwards compatible to Category 3, 5, and 5e:** Supports lower category installations and components.

### specifications

#### General Info

Cable Type: Four-pair stranded UTP non-plenum  
Color Cable Jacket: Green

Termination: 8-Pos Mod

Typical Applications: IEEE 802.3 10GBase-T, 1000Base-T (Gigabit Ethernet), TIA/EIA-854 1000Base-TX, ATM CB1G

### **Listing Agencies/Third Party Information**

FCC Standard: Yes

### **Construction Information**

Component1: Cable

Component2: Eight-position plug assembly

Component3: Modular plug IDC contacts

Component4: Paralign 2 pair segregation and strain relief

Finish Plating2: Internal metallic barrier

Finish Plating3: 50 Micro inch elective gold plating over nickel

Material1: 26 AWG bare copper stranded conductors, PVC insulation, PVC jacket

Material2: Polycarbonate plug housing and conductor positioning sled

Material3: Phosphor-bronze contacts

Material4: Molded Polypropylene Copolymer

### **Dimensions**

Diameter Metric: 7.5 mm

Diameter U S: 0.29"

Length Metric: 5.57 m

### **Cord Information**

Connector Type End One: Plug, HSG, eight-contact, RJ45, high performance with 10G internal barrier

Connector Type End Two: Plug, HSG, eight-contact, RJ45, high performance with 10G internal barrier

Jacket Color: Green

Jacket Rating: CM

Cord Length U S: 15'

Min Bend Radius: 1.20"

Pinning: Straight 1-1, 2-2, 3-3, etc.

### **Technical Information**

Category Rating: Category 6A

Ohm Value: 100

Performance Rating: 10G UTP

Sort Termination: 3

Wire Gauge: 26 AWG