


Clarity 5E 24-port panel, Cat5e, six-port modules, 19" x 1.75"

OR-PHD5E6U24



Clarity 5E 24-Port High Density Patch Panel is component compliant to EIA/TIA Category 5e performance requirements. It occupies one rack unit and measures 19" x 1.75". Jacks are grouped in six-port modules. Part of the Clarity 5E link and channel solution that provides significant installed performance headroom.

features & benefits

- **ETL verified to TIA Category 5e component spec:** Elevated component performance.
- **Center tuned to Clarity 5E patch cords:** More transparent mated union.
- **Universal wiring:** Supports T568A and T568B installs.
- **Easy lace 110 termination:** Saves installation time.
- **Supplied rear cable management:** Supports good cabling practice.
- **High density design:** Maximizes rack utilization.
- **RoHS compliant:** Lead free.



specifications

General Info

Mod Jack Wiring: Universal T568A/B
Number Of Ports: 24

Listing Agencies/Third Party Information

CUL Listing No: E131600
ETL Listing No: 3013270-004
UL Listing No: E131600

Construction Information

Component1: Panel
Component2: Six-port jack housing
Component3: Six-port rear IDC housing
Component4: Array of eight modular dual reactance contacts
Component5: IDC contacts (low noise)
Finish Plating1: Painted black texture with green silkscreen
Finish Plating4: Nickel plating and a minimum of 50 micro inches of selective gold plating in contact area
Finish Plating5: Nickel plating with tin over plate
Material1: .094" Aluminum
Material2: High impact thermoplastic UL 94V-0
Material3: Polycarbonate
Material4: Beryllium copper
Material5: Phosphor Bronze

Dimensions

Cable Diameter Range: 22-26 AWG
Depth Metric: 3.175 mm
Height Metric: 44.45 mm
Height U S: 1.75 in
Width Metric: 482.6 mm

Technical Information

Category Rating: Category 5e
Performance Rating: Category 5e

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant