

Clarity Cat6a 48 port angled panel, 110/6port, T568A/B, 3.5 x 19, HD

OR-PHA6AU48



Clarity 6A 48-Port Angled Patch Panel is component compliant to EIA/TIA Category 6a performance requirements. High density design occupies 2 rack units, measuring 19" x 3.5". Jacks are grouped in six-port modules. Part of the Clarity 6A link and channel solution that provides significant installed performance headroom.

# features & benefits

- ETL verified to TIA Category 6A component spec: Elevated component performance.
- Center tuned to Clarity 6A/10G patch cords: More transparent mated union.
- Universal wiring: Supports T568A and T568B installs.
- Easy lace 110 termination: Saves installation time.
- Supplied rear cable management: Supports good cabling practice.
- Angled high density design: Optimum use of rack space.
- RoHS compliant: Lead free.



# specifications

# **General Info**

Category Performance Application: Category 6a/UTP

Color Cable Jacket: Yes

Mod Jack Wiring: Universal T568A/B

Number Of Ports: 48

## **Listing Agencies/Third Party Information**

CUL Listing No: E131600

ETL Listing No: 100369245CRT-001F

ETL Standard: Yes FCC Standard: Yes

UL Listing No: E131600 UL Standard: Yes

#### **Construction Information**

Component1: Panel

Component2: Six-port jack housing Component3: Six-port rear IDC housing

Component4: Array of eight modular dual reactance contacts

Component5: IDC contacts (low noise)

Finish Plating1: Painted black texture with yellow / black overlay

Finish Plating4: Nickel plating and a minimum of 50 micro inches of selective gold plating in contact area

Finish Plating5: Nickel plating with tin over plate

Material1: .090" Steel

Material2: High impact thermoplastic UL 94V-0

Material3: Polycarbonate Material4: Beryllium copper Material5: Phosphor Bronze

### **Dimensions**

Cable Diameter Range: 22-25 AWG

Depth Metric: 60.70mm Height Metric: 88.9 mm Height U S: 3.5 in Rack Units: 2

Width Metric: 482.6 mm

Width US: 19 in

#### **Technical Information**

Category Rating: Category 6a Performance Rating: Category 6a

Wire Gauge: 22-25 AWG