


# TracJack Faceplate, four-port (single gang), plastic, Electrical Ivory

OR-40300546-13



Ortronics Single Gang Plastic Faceplates accept front-loading TracJack modules and include two snap-in label fields

## features & benefits



- **Low profile design:** Blends with most environments.
- **Recessed label fields:** Supports TIA/EIA 606 standard.
- **Easily accepts snap-in TracJacks:** Easily field configured.
- **Front-load module approach:** Improves access for future work.
- **Textured finish:** Hides future scuffs.
- **Oval mounting holes:** Assists proper alignment

## specifications

**General Info**

Category Performance Application: Single gang  
Color: Electrical Ivory  
Footprint: TracJack  
Number Of Ports: 4 -port

**Assembly/Installation Information**

Mounting Hardware Included: #6-32\*25 mm Screw, Binding Head (2 ea)

**Listing Agencies/Third Party Information**

CUL Listing No: E131600  
UL Listing No: E131600  
UL Standard: Yes

**Construction Information**

Component1: Plastic TracJack Faceplate  
Material1: High Impact Thermoplastic 94V-0 ABS/PC/BLEND

**Dimensions**

Depth Metric: 7.62 mm  
Height Metric: 114.3 mm  
Height U S: 4.5"  
Width Metric: 69.85 mm

**Buy American Act Compliance**

Country of Origin: TAIWAN  
Buy American Act Status: Trade Agreement Act Compliant