

TracJackPlastic Surface Mount Box for four modules

OR-40400072



Replaced By 404TJ2X2TracJack Plastic
Surface Mount Box for two modules

features & benefits



- Low profile design
- Base plate and snap-on cover design
- Front-load module approach
- Recessed label fields
- Textured finish
- Holds four TracJack modules

specifications

General Info

Category Performance Application: Up to four modules

Color: Fog White

Footprint: TracJack

Assembly/Installation Information

Mounting Hardware Included: #6-20*19 mm (Panhead) (2 ea)

Listing Agencies/Third Party Information

CUL Listing No: E131600

UL Listing No: E131600

UL Standard: Yes

Construction Information

Component1: Plastic TracJack Surface Box

Material1: High Impact Thermoplastic ABS 94V-0

Dimensions

Depth Metric: 29.46 mm

Height Metric: 61.47 mm

Height U S: 2.42"

Width Metric: 89.41 mm