

TracJack 106-Type Frame, four-port, Fog White

OR-40800019



TracJack 106-Type Plastic Duplex Frame that accepts four front-loading TracJack modules. It is compatible with many cable delivery systems that can house electrical duplex outlets

features & benefits

- **Matches duplex electrical outlet footprint:** Supports use with electrical delivery system.
- **Field configurable with TracJacks:** Design or site flexibility for new or retrofit.
- **Supports TracJack footprint:** Broad offering of connector options.
- **Front load and access:** Connector access without removing plate.
- **Choice of four colors:** Compatible with many environments.



specifications

General Info

Category Performance Application: Single gang
Color: Fog White
Footprint: TracJack
Number Of Ports: 4-port

Assembly/Installation Information

Mounting Hardware Included: #6-32*25 mm Screw, Binding Head (2 ea)

Listing Agencies/Third Party Information

CUL Listing No: E131600
UL Listing No: E131600
UL Standard: Yes

Construction Information

Component1: Plastic TracJack Mounting Frame
Material1: High Impact Thermoplastic ABS 94V-0

Dimensions

Depth Metric: 11.43 mm
Height Metric: 103.88 mm
Height U S: 4.09"
Width Metric: 44.45 mm

Buy American Act Compliance

Country of Origin: TAIWAN
Buy American Act Status: Trade Agreement Act Compliant