

32-port T1 panel, RJ48X keyed jacks with shorting bar to 110

OR-809045047



T1 Network Interface Panel, 32-port RJ48X (8P8C) keyed jacks with shorting bar wired to 110-type connectors.

features & benefits

- **RJ48X:** Supports T1 applications.
- **110 termination:** Easy and reliable termination.



specifications

General Info

Mod Jack Wiring: RJ48X
Number Of Ports: 32

Listing Agencies/Third Party Information

CSA Listing Info: LR 90894
CUL Listing No: E131600
UL Listing No: E131600

Construction Information

Component1: Panel
Component2: RJ48X keyed jack housing
Component3: Modular jack contacts
Component4: Jack bracket
Component5: 50/75-pair 110 bracket

Finish Plating1: Painted black - texture, with white silkscreen
Finish Plating3: 50 micro inch gold or GTX
Material1: 0.125" Aluminum
Material2: ABS UL94V-0
Material3: Phosphor Bronze
Material4: 0.062" Aluminum
Material5: 0.063" Aluminum

Dimensions

Cable Diameter Range: 22-26 AWG
Depth Metric: 3.175 mm
Height Metric: 88.9 mm
Height U S: 3.5 in
Width Metric: 482.6 mm

Technical Information

Performance Rating: T1

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant