

TechChoice Angled Patch Panel Category 6 24 Port

OR-SPA6U24



TechChoice patch panels combine the reliability and ease of installation you'd expect from Legrand | Ortronics with performance and rugged construction to provide a cost-effective option for communications technicians.



features & benefits

- **Recessed angled design:** Directs cords more easily to vertical management.
- **Third party tested:** Meets component specifications for TIA/EIA-568-B.2 and ISO11801-202.
- **High density design:** Maximizes rack utilization.
- **Universally wired 110 termination:** Supports T568A and T568B installations.
- **Front designation labeling kits:** Easily identify infrastructure and meet TIA/EIA-606-A standard.
- **RoHS compliant:** Lead free.

specifications

General Info

Category Performance Application: Category 6
Color: Black
Footprint: Keystone
Mod Jack Wiring: Universal T568A/B
Number Of Ports: 24
Performance Category: Category 6

Listing Agencies/Third Party Information

CUL Listing No: E131600
UL Listing No: E131600
UL Standard: Yes

Dimensions

Cable Diameter Range: 22-26 AWG
Depth Metric: 50.8
Depth U S: 2
Height Metric: 44.45
Height U S: 1.75
Rack Units: 1RU
Width Metric: 482.5989999999999
Width U S: 19

Technical Information

Category Rating: Cat 6
Performance Rating: TechChoice patch panels utilize a unique snap-in six-port module and are available in 24- and 48-port configurations.

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant