

Momentum 2 Cassette, single-mode fiber, 1U, 12 fibers, LC duplex connectors

OR-M2LCD12-09



Momentum 2 modular fiber optic pre-terminated cassettes provide the fastest method of structured cabling deployment: plug it in and you're ready to go. Factory-terminated and tested cassettes guarantee field performance.



features & benefits

- **Compact, pre-terminated modular system::** Provides quick and easy deployment, moves, adds and changes, eliminating costly field installation time.
- **12- and 24-fiber 1 unit modular cassettes:** Maximum port density conserves space.
- **Best-in-class 10GBASE-SR 10 Gbe performance:** Low insertion loss combined with ultra low differential mode delay (DMD) enhances 10 Gig performance.
- **Unsurpassed optical performance:** Lowest insertion loss cassette modules support high optical performance in installed links.
- **High fiber count backbones available:** MTP to MTP ribbon backbone cables offered in 12, 24, 48 and 72-fiber count options.
- **Common cassette mounting footprint:** Fits in all Ortronics rack mount cabinets and raised floor patch panels.

specifications

Technical Information

Product Fits Into: FC Series rack mount fiber cabinets

Buy American Act Compliance

Country of Origin: TAIWAN

Buy American Act Status: Trade Agreement Act Compliant