

ST Field Terminating, single mode, 900 micron buffer, individual pack

OR-205KAS9EA-09



ST Field Terminating, single mode, 900 micron buffer, individual pack. OptiMo field-installable ST connector, for use with single mode fiber, incorporates a factory-bonded fiber stub, ceramic ferrule, and precise factory polish.

features & benefits

- Factory produced connector polish
- Factory polish process monitored using advanced laser interferometry
- No polishing required in the field
- No epoxy required
- Unlimited shelf life connector
- 62.5/125, Enhanced 50/125 and single mode options
- Lightweight, convenient Termination Kit



specifications

Cord Information

Fiber Type: 62.5/125
Finish End One: Physical Contact-PC

Technical Information

Field Assembly Time: 1 minute on 900 micron buffer, 3 minutes on jacketed cable
Operating Temperature Fahrenheit: 32 to 131 degrees F (0 to + 55 degrees C)
Storage Temperature: -40 to + 104 degrees F (-40 to + 40 degrees C)
Typical Insertion Loss: 0.30000001
Typical Return Loss: -30

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant