

SC Field Terminating, 50/125, 900 micron buffer, individual pack

OR-205KAS9FA-50T



SC Field Terminating, 50/125, 900 micron buffer, individual pack. OptiMo 10Gb/s field-installable SC connector, for use with 50 micron multimode fiber, is suitable for 10 Gigabit applications. The OptiMo 10Gb/s technology incorporates a factory-bonded fiber stub, ceramic ferrule, and precise factory polish.



features & benefits

- Factory produced connector polish
- Factory polish process monitored using advanced laser interferometry
- No polishing required in the field
- No epoxy required
- Unlimited shelf life connector
- 62.5/125, Enhanced 50/125 and single mode options
- Lightweight, convenient Termination Kit

specifications

Cord Information

Fiber Type: 50/125, Enhanced Bandwidth (10Gig)
Finish End One: Physical Contact-PC

Technical Information

Field Assembly Time: 1 minute on 900 micron buffer, 3 minutes on jacketed cable
Operating Temperature Fahrenheit: 32 to 131 degrees F (0 to + 55 degrees C)
Storage Temperature: -40 to + 104 degrees F (-40 to + 40 degrees C)
Typical Insertion Loss: 0.30000001
Typical Return Loss: -30

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant