

High Density, Low Profile, Rack Mount Fiber Cabinet for Patching

OR-625MMC-24PE1RB



This pre-loaded cabinet secures, protects, and organizes up to 24 single mode optical terminations. The cabinet also provides interconnect or cross connect facilities between horizontal and backbone inside plant (ISP) or outside plant (OSP) cables.



features & benefits

- Pre-loaded with fiber optic adapters
- Slide-out fiber management drawers
- Includes bend limiters at patch cord exits
- Universal mounting brackets suitable for 19" and 23" installation
- Internal bend limiting clips provided
- 1.5" deep front shelf
- Top panel removable
- Rear door opens with quarter-turn fasteners
- 1.75" openings in the top and bottom
- Smoked, shatterproof plexi door with lock

specifications

General Info

Number Of Ports: 12
Typical Applications: Single Mode

Assembly/Installation Information

Mounting Hardware Included: Yes

Dimensions

Depth Metric: 343
Height Metric: 44

Height U S: 1.75
Rack Units: 1
Width Metric: 483

Cord Information

Fiber Type: single mode

Technical Information

Fiber Capacity: 24
Rack mm: 44
Rack Inches: 1.75

Buy American Act Compliance

Country of Origin: UNITED-STATES-OF-AMERICA
Buy American Act Status: Buy American Act Compliant