

## High Density, Low Profile, Rack Mount Fiber Cabinet for Patching

OR-625MMC-24PL1RB



This pre-loaded cabinet secures, protects, and organizes up to 12 multimode optical terminations. The cabinet also provides interconnect or cross connect facilities between horizontal and backbone inside plant (ISP) or outside plant (OSP) cables. Unit supplied pre-loaded with 12 beige LC adapters containing phosphor-bronze alignment sleeves, suitable for multimode applications. Face recessed, fiber capacity: 24



### features & benefits

- Pre-loaded with fiber optic adapters
- Slide-out fiber management drawers
- Includes bend limiters at patch cord exits
- Universal mounting brackets suitable for 19" and 23" installation
- Internal bend limiting clips provided
- 1.5" deep front shelf
- Top panel removable
- Rear door opens with quarter-turn fasteners
- 1.75" openings in the top and bottom
- Smoked, shatterproof plexi door with lock

### specifications

**General Info**

Number Of Ports: 12

Typical Applications: Multimode

**Assembly/Installation Information**

Mounting Hardware Included: Yes

**Dimensions**

Depth Metric: 343

Height Metric: 44

Height U S: 1.75

Rack Units: 1

Width Metric: 483

**Technical Information**

Fiber Capacity: 24

Rack mm: 44

Rack Inches: 1.75

**Buy American Act Compliance**

Country of Origin: UNITED-STATES-OF-AMERICA

Buy American Act Status: Buy American Act Compliant