

# MM10 Vertical Cable Management Cage, with door, 16" x 13" x 7'

OR-MM10VMD816



MM10 Vertical Cable Management Cage,  
with door, 16" x 13" x 7', black

## features & benefits



- **Vertical cage with individual rack unit fingers has a fill capacity of 1340 Category 6 patch cords and 948 10Gig patch cords:** Provides organized method for routing and storage of patch or cross connect cable between racks.
- **Hinged extruded aluminum front door:** The door allows easy access during moves, adds and changes.
- **Mounted on the front flange between the Mighty Mo 6 racks when two or more are installed in a row:** Creates a 8.25" channel between racks for front to back routing of equipment cables and patch cords.
- **Supplied with four slack storage spools and 12 bend limiting clips:** Adjustable bend limiting control for copper and fiber cords.
- **All necessary mounting hardware included:** Hanger clips hold the cage in place for easy and quick one person installation.

## specifications

### Construction Information

Component1: Vertical management cage  
Component2: Cable management finger sections  
Component3: Bearing Plate  
Component4: Cover  
Component5: Latch  
Finish Plating1: Powdercoat black  
Finish Plating2: Black  
Finish Plating3: Black  
Finish Plating4: 6063-T6 Aluminum

Finish Plating5: Black  
Material1: .1875 Wire  
Material2: Polycarbonate  
Material3: Polycarbonate  
Material4: 6063-T6 Aluminum  
Material5: 6063-T6 Aluminum

### **Dimensions**

Depth Metric: 330 mm  
Height Metric: 2.2 m  
Height U S: 89.62"  
Width Metric: 416 mm

### **Technical Information**

Patent No: 6,946,605 6,968,647 7,026,553

### **Buy American Act Compliance**

Country of Origin: UNITED-STATES-OF-AMERICA  
Buy American Act Status: Buy American Act Compliant