


A World of Security Communication




PA equipment can be integrated to allow for AN-8000 stations to perform paging to any pre-determined locations. Using the multi-interface unit (AN-8000MI) allows routing of multiple BGM inputs to any number of stations,

security requirements. The system's "Echo Cancellation" feature provides hands-free duplex conversations between stations without feedback or clipping. External

full CCTV call-up, and centralized door release. Door stations also provide local open-collector output for controlled access to guarantee that your security never becomes compromised.





Master Stations

AN-8010MS Standard Handset Master Station

Features:

- · Hands-free or handset communication
- · Keypad for calling
- 5 programmable "one touch" dialing assignments
- Paging
- · Door release
- · Call transfer

AN-8000MS Multifunctional Handset Master Station with LCD display

Features:

Same features as AN-8010MS plus...

- LCD display (2 lines of 16 characters)
- External speaker and headset ports
- · Limited programming capabilities
- 8 auto-dial buttons

AN-8011MS Open Voice Master Station

Features:

- Hands-free communication
- · Compact size
- · Keypad for calling
- · 8 function buttons
- Paging
- · Door release
- · Call transfer



Features:

- Heavy-duty design for industrial use and adverse environments
- Hands-free or handset communication
- External speaker port
- Temp. range of -10° C to 50° C
- Dry contacts when call is placed/received
- Keypad for calling
- · 8 function buttons

AN-8031MS

Flush Mount Master Station



Features:

- · Hands-free communication
- · Port for optional RS-191 handset
- · Footswitch speed dial inputs
- Keypad for calling
- · 8 function buttons
- · Flush mount (5-gang)

AN-8500MS

IP Multifunctional Handset Master Station with LCD display



Features:

Same features as AN-8000MS plus...

- Does not require AN-8000EX
- · Connects directly to LAN or WAN
- Occupies one network node
- Supports PoE (802.3af)
- External speaker and headset ports
- Limited programming capabilities
- · 8 auto-dial buttons

Door Stations

AN-8050DS Flush Mount

Door Station \$

Features:

- · Indoor use only
- · Hands-free full duplex communication
- Flush mount (3-gang)
- IP-54 rated
- · Door release open collector output (30VDC, 50mA)

AN-8050DSW Features:

Flush Mount **Door Station**



· Weather resistant

- Hands-free full duplex communication
- Flush mount (3-gang)
- IP-54 rated
- · Door release open collector output (30VDC, 50mA)

AN-8540DS

IP Flush Mount **Door Station**

Does not require AN-8000EX

Features:



- . Connects directly to LAN or WAN
- Occupies one network node

Same features as AN-8050DS plus..

- Supports PoE (802.3af)
- Door release open collector output (30VDC, 50mA)

Exchange & Multi-Interface Units

AN-8000EX

Network Intercom



AN-8000MI

Multiple Interface Unit



Features:

- 16 Stations per exchange
- 2 paging outputs per exchange (0dB, 600Ω)
- 2 paging control outputs per exchange (24VDC, 500mA)
- 10 BASE-T or 100 BASE-TX network connection (RJ45)
- 4 internal and 8 external communication links
- EIA standard rack (1 U) mountable)

Features:

- Two outputs / inputs for audio distribution
- 16 input and output programmable relays
- 2 PBX inputs (E & M interface)
- External equipment control
- Calling station indication / CCTV interlock
- Contact Bridge
- · Paging input / output
- Background music input
- EIA standard rack (1 U) mountable)





YC-280 Wall bracket for AN-8000MS, AN-8010MS and AN-85000MS



YC-290 Wall bracket for AN-8011MS and AN-8020MS

RS-191

Handset used with AN-8031MS, wall mount **YS-13A**

YC-251

3-gang surface mount back box for AN-8031MS

AD-1210P

12V DC, 1A power supply for IP

System Features

- Network-based intercom system consisting of an exchange unit and dedicated master and door stations.
- Single exchange can connect any combination of door and master stations up to 16 units.
- Up to 80 exchanges can be included on a system for a total of 1280 communication devices.
- IP Direct master station (AN-8500MS) and vandal resistant door station (AN-8540DS), connect directly to a LAN/WAN and do not require an exchange unit.
- Efficient method of communicating over local or wide area network using existing infrastructure.
- Full complement of PC Programmable functions and features. Some of them include: Redial, Recall, Auto-Dialing, Group Call, Group Searching, Absence Transfer, Call Forwarding, Call Hold, and Scan Monitor.

- Automatic echo cancellation prevents clipping and ghosting during hands-free simultaneous conversation.
- Adjustable microphone and speaker levels on all stations for high ambient noise areas.
- Stations incorporate a built-in speaker to allow paging through the units.
- Paging through overhead speaker network using an external amplifier with total broadcast capabilities of up to 160-zones with paging and all-call paging.
- Total system maintenance can be performed off-site using a personal computer with provided software.
- 7kHz* communication frequency provides better clarity than most telephones.
- System occupies a very low amount of bandwidth.

AN-8031MS


4-1/2


9/16


YC-290


network status may cause audio quality to temporarily deteriorate to 3.4 kHz


Unit Dimensions















2-13/16









AN-8000MS, AN-8500MS, AN-8010MS


AN-8050DS AN-8050DSW. AN-8540DS

0

4-1/2"

6-7/16"

, **e** e e



10-3/16"

1-1/4"

Distributed by:





Aiphone Co. Ltd.







1700 130th Ave. NE Bellevue, WA 98005 Ph: (800) 692-0200 Fax: (425) 455-0071 www.aiphone.com

AIPHONE