

AXIS ACH13HB Outdoor Housing

Weatherproof your Axis Network Cameras



The AXIS ACH13HB Outdoor Housing provides protection for Axis network cameras in both hot and cold climates. The housing was designed to meet IP65 standard of protection.

The body is constructed of an attractive white finished aluminum with black end caps.

The housing ships with a 24VAC heater and blower that enables the Axis network camera to operate in temperatures from -20°F to $+120^{\circ}\text{F}$.



- Indoor and outdoor models
- IP65- rated protection
- 24 VAC heater and blower
- Side hinge for easy access when servicing

AXIS ACH13HB Outdoor Housing

Technical Data – Housing

General

- Made of aluminum
- White finish with black end caps
- Two watertight strain relief valves for network and power cables
- For use with AXIS 211 and AXIS 221 Network Camera

Electrical

- 24 VAC, 50/60 Hz
- Heater: 24 VAC, 25 vA, 1.04 Amps
- Blower: 24 VAC, input (RECTIFIED), 1.4 vA
- 24 VAC to 12 VDC transformer, 1.0 Amp

Dimensions and Weight

- Product measurements
Weight (excluding power supply): 4 lbs
Dimensions (H x W x D): 15.25 x 4.33 x 5.5 inches
- Shipping measurements
Weight: 5 lbs
Dimensions (H x W x D): 17 x 5 x 6 inches

Operating Conditions

- Indoor/outdoor (Indoor version with no electronics available)
*The indoor model does not include:
Heater or blower;
24vac to 12vdc power supply;
Sunshield
Works with the AXIS 210 Network Camera*
- IP65 rated (with cable glands)
- Operating Temperature -20 F to +120 F

Approvals

- CE
- UL Listed
- 24 VAC, 40 VA Power Supply
- Integrated Sunshield
- Heater and Blower
- Installation Guide

www.axis.com